



### Features

- ▶ Homogenizer of rotor/stator type and possible to do quick Homogeneous and dispersion
  - ▶ Sample inserted into the rotor inside is circulated repeatedly through the narrow slit between rotor and stator, and emulsified, homogenized, mixed and pulverized thru dispersion by strong rotor.
  - ▶ Easy to change various rotor and stator by a driver only what you want to use
  - ▶ High quality tools dispersed durability (Stainless steel 316L)
  - ▶ easy to stick and take off for cleaning
- \*Fixing clamp (option)

### Specifications

Model	SR30
Motor(input/output)	670/340W
Working Capacity	10~2000ml
Speed Range	3700~27000rpm
Speed Adjustment	Stepless
Speed Display	Scale
Dimensions (W×D×H)	75×75×255mm
Weight	1.9Kg
Electrical Supply	AC 220V 50/60Hz

※ Note : set ⇒ Homogenizer(SR30) + Tool(Ø20 Standard) + Stand(PS80) + Clamp(CH320)

### Dispersing tools

Model	Shaft Ø
T8SF	Ø8mm
T10SF	Ø10mm
T20SC, T20CC, T20MC	Ø20mm
T20SF, T20CF, T20MF, T20EF	
T30SC, T30CC, T30MC	Ø30mm
T30SF, T30CF, T30MF, T30EF	

Rotor	Ø20mm (Only)
Rotor	Ø30mm (Only)